

PSU 19" AC/DC Maxpower 50 W, Single



Redundancy with active OR decoupling; No base load required; Automatic load distribution depending on PSU temperature; No current share line required between power supplies; Quasi-resonant topology reduces EMC emissions.

CERTIFICATIONS



CARACTERISTICI

Wide input voltage range 90 ... 253 VAC and 100 ... 360 VDC

1 output voltage

Signalling: Output voltage OK

Including front panel

Standby (no load) Power <1.5 W

Efficiency up to 88%

SPECIFICAȚII

Table 1/2

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-172	19" Switched-Mode	90 – 264V	50W	1	15V	3.4A
13100-173	19" Switched-Mode	90 – 264V	50W	1	24V	2.1A

Număr de catalog	Type	Input Voltage AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-170	19" Switched-Mode	90 – 253V	50W	1	5V	10A
13100-171	19" Switched-Mode	90 – 264V	50W	1	12V	4.2A
13100-174	19" Switched-Mode	90 – 264V	53W	1	48V	1.1A

Table 2/2

Număr de catalog	Rack Height	Rack Width	Package Quantity	Quick Ship
13100-172	3U	6HP	1	No
13100-173	3U	6HP	1	No
13100-170	3U	6HP	1	No
13100-171	3U	6HP	1	No
13100-174	3U	6HP	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Output data at Ta= -25 ... 50 °C.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE