

PSU 19" AC/DC for VMEbus



Pluggable 19" Power Supply for VMEbus applications.

CERTIFICATIONS



CARACTERISTICI

Wide input voltage range 90 ... 264 VAC and 130 ... 350 VDC with active power factor correction (PFC)

VMEbus signalling

3 output voltages

SPECIFICAȚII

Table 1/3

Număr de catalog	Type	Works With	Input Voltage AC	Power	Number of Output Voltages	Voltage 1
13100-205	19" Switched-Mode	VMEbus Systems	90 – 264V	150W	3	5V
13100-204	19" Switched-Mode	VMEbus Systems	90 – 264V	224W	3	5V
13100-203	19" Switched-Mode	VMEbus Systems	90 – 264V	224W	3	5V

Table 2/3

Număr de catalog	Current 1	Voltage 2	Current 2	Voltage 3	Current 3	Rack Height
13100-205	20A	12V	4A	-12V	3A	6U
13100-204	28A	15V	5.6A	-15V	2.4A	6U
13100-203	28A	12V	7A	-12V	3A	6U

Table 3/3

Număr de catalog	Rack Width	Depth	Package Quantity	Quick Ship
13100-205	8HP	171.93mm	1	No
13100-204	12HP	171.93mm	1	No
13100-203	12HP	171.93mm	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Output data at TU = 0 ... 40 °C.

Output power V2 + V3 = 60 W.

Output currents (UL values in bracket): V1 = 5 V / I1 = 20 A (18 A) V2 = 12 V / I2 = 4 A (3 A) V3 = -12 V / I3 = 3 A (2 A).

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE