

PSU 19" DC/DC Coolpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications.

CERTIFICATIONS



CARACTERISTICI

Wide input voltage range from 20 to 72 VDC

Galvanic separation between primary and secondary circuits

High power density

External ON/OFF

SPECIFICAȚII

Table 1/2

Număr de catalog	Type	Input Voltage DC	Power	Number of Output Voltages	Voltage 1	Current 1
13103-002	19" DC/DC Converter	20 – 72V	100W	1	5V	20A
13103-004	19" DC/DC Converter	20 – 72V	100W	1	15V	6.7A
13103-003	19" DC/DC Converter	20 – 72V	102W	1	12V	8.5A

Table 2/2

Număr de catalog	Rack Height	Rack Width	Depth	Package Quantity	Quick Ship
13103-002	3U	6HP	171.93mm	1	No
13103-004	3U	6HP	171.93mm	1	No
13103-003	3U	6HP	171.93mm	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order front panel separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE