

Socket Strip, SCHUKO



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

CERTIFICATIONS



CARACTERISTICI

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFICAȚII

Material: Aluminiu; Polyamide

Color: Grey

Product Type: Socket Strip

Table 1/2

Număr de catalog	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
------------------	-------------	-----------------	------------------	------------	----------	------------------

60110-200	SCHUKO	3	No	230V		1
60110-201	SCHUKO	4	No	230V		1
60110-202	SCHUKO	9	No	230V		1
60110-206	SCHUKO	8	Yes	230V		1
60110-210	SCHUKO	8	No	230V	Transient Protection	1
60110-214	SCHUKO	7	No	230V	Mains Suppression Filter	1
60110-266	SCHUKO	6	No	230V	Transient Protection, Mains Suppression Filter	1
60110-203	SCHUKO	12	No	230V		1
60110-204	SCHUKO	15	No	230V		1
60110-205	SCHUKO	19	No	230V		1
60110-207	SCHUKO	12	Yes	230V		1
60110-208	SCHUKO	15	Yes	230V		1
60110-209	SCHUKO	19	Yes	230V		1
60110-211	SCHUKO	9	No	230V	Transient Protection	1
60110-212	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-216	SCHUKO	6	No	230V	Fault Current Protection	1
60110-217	SCHUKO	6	No	230V	Fault Current Protection, Overcurrent Protection	1

Table 2/2

Număr de catalog	Depth	Finish	Length	Quick Ship
60110-200	44mm	Anodized	184mm	No
60110-201	44mm	Anodized	210mm	No
60110-202	44mm	Anodized	438.5mm	No
60110-206	44mm	Anodized	438.5mm	No
60110-210	44mm	Anodized	438.5mm	No
60110-214	44mm	Anodized	438.5mm	No
60110-266	44mm	Anodized	438.5mm	No
60110-203	44mm	Anodized	947.5mm	No
60110-204	44mm	Anodized	1202mm	No
60110-205	44mm	Anodized	1753mm	No
60110-207	44mm	Anodized	947.5mm	No
60110-208	44mm	Anodized	1202mm	No
60110-209	44mm	Anodized	1753mm	No
60110-211	44mm	Anodized	947.5mm	No
60110-212	75mm	Anodized	438.5mm	No
60110-216	88mm	Anodized	438.5mm	No
60110-217	88mm	Anodized	438.5mm	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please order mounting bracket for vertical mounting separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE