

# Socket Strip, UTE



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with UTE outlets.

## CERTIFICATIONS



## CARACTERISTICI

230 V, 16 A

In accordance with NFC 61-303

Socket strip with UTE sockets

Mounting height 1 U

Horizontal or vertical mounting

Connecting cable 2 m, with SCHUKO/UTE plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

## SPECIFICAȚII

**Material:** Aluminiu; Polyamide

**Color:** Grey

**Product Type:** Socket Strip

Table 1/2

| Număr de catalog | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function | Package Quantity |
|------------------|-------------|-----------------|------------------|------------|----------|------------------|
|------------------|-------------|-----------------|------------------|------------|----------|------------------|

|           |     |    |     |      |                                                  |   |
|-----------|-----|----|-----|------|--------------------------------------------------|---|
| 60110-220 | UTE | 4  | No  | 230V |                                                  | 1 |
| 60110-221 | UTE | 9  | No  | 230V |                                                  | 1 |
| 60110-225 | UTE | 8  | Yes | 230V |                                                  | 1 |
| 60110-267 | UTE | 6  | No  | 230V | Transient Protection, Mains Suppression Filter   | 1 |
| 60110-227 | UTE | 8  | No  | 230V | Transient Protection                             | 1 |
| 60110-229 | UTE | 7  | No  | 230V | Mains Suppression Filter                         | 1 |
| 60110-222 | UTE | 12 | No  | 230V |                                                  | 1 |
| 60110-223 | UTE | 15 | No  | 230V |                                                  | 1 |
| 60110-224 | UTE | 19 | No  | 230V |                                                  | 1 |
| 60110-226 | UTE | 12 | Yes | 230V |                                                  | 1 |
| 60110-228 | UTE | 6  | No  | 230V | Overcurrent Protection                           | 1 |
| 60110-230 | UTE | 6  | No  | 230V | Fault Current Protection                         | 1 |
| 60110-231 | UTE | 6  | No  | 230V | Fault Current Protection, Overcurrent Protection | 1 |

Table 2/2

| Număr de catalog | Depth | Finish   | Length  | Quick Ship |
|------------------|-------|----------|---------|------------|
| 60110-220        | 44mm  | Anodized | 210mm   | No         |
| 60110-221        | 44mm  | Anodized | 438.5mm | No         |
| 60110-225        | 44mm  | Anodized | 438.5mm | No         |

| Număr de catalog | Depth | Finish   | Length  | Quick Ship |
|------------------|-------|----------|---------|------------|
| 60110-267        | 44mm  | Anodized | 438.5mm | No         |
| 60110-227        | 44mm  | Anodized | 438.5mm | No         |
| 60110-229        | 44mm  | Anodized | 438.5mm | No         |
| 60110-222        | 44mm  | Anodized | 947.5mm | No         |
| 60110-223        | 44mm  | Anodized | 1202mm  | No         |
| 60110-224        | 44mm  | Anodized | 1753mm  | No         |
| 60110-226        | 44mm  | Anodized | 947.5mm | No         |
| 60110-228        | 75mm  | Anodized | 438.5mm | No         |
| 60110-230        | 88mm  | Anodized | 438.5mm | No         |
| 60110-231        | 88mm  | Anodized | 438.5mm | No         |

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order bracket for vertical mounting separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**