

# Varistar CP Base Plate, One-Piece, With Lateral Cable ducting, Mobile

Varistar CP Base Plate, One-Piece, With Lateral Cable ducting.



## CARACTERISTICI

Base plate mobile is open at the side; the opening can be covered over with a brush strip

## SPECIFICAȚII

**Product Type:** Cabinet/Rack Base

**Material:** Oțel

Table 1/2

| Număr de catalog | Width | Depth  | Package Quantity | Color      | Color Code | Finish         |
|------------------|-------|--------|------------------|------------|------------|----------------|
| 21630-158        | 600mm | 1000mm | 1                | Black Grey | RAL 7021   | Vopsit Pulbere |
| 21630-163        | 800mm | 1200mm | 1                | Black Grey | RAL 7021   | Vopsit Pulbere |
| 21630-162        | 800mm | 1100mm | 1                | Black Grey | RAL 7021   | Vopsit Pulbere |
| 21630-161        | 800mm | 1000mm | 1                | Black Grey | RAL 7021   | Vopsit Pulbere |
| 21630-160        | 600mm | 1200mm | 1                | Black Grey | RAL 7021   | Vopsit Pulbere |
| 21630-159        | 600mm | 1100mm | 1                | Black Grey | RAL 7021   | Vopsit Pulbere |

Table 2/2

| Număr de catalog | Type                      | Quick Ship |
|------------------|---------------------------|------------|
| 21630-158        | Base Plate, Cable Ducting | No         |
| 21630-163        | Base Plate, Cable Ducting | No         |
| 21630-162        | Base Plate, Cable Ducting | No         |
| 21630-161        | Base Plate, Cable Ducting | No         |
| 21630-160        | Base Plate, Cable Ducting | No         |
| 21630-159        | Base Plate, Cable Ducting | No         |

## DETALII SUPLIMENTARE DESPRE PRODUS

Please order brush strip separately.

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Portofoliul nostru puternic de mărci:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**