

Varistar CP Bottom Rear Panel, Shortened



Shortened Rear Panel available for IP20, IP55 and EMC applications.

Shortened rear panels ensure efficient cable management.

CARACTERISTICI

Screw fixed, Robust and Single person mountable Side Panel

Plain or with brush strip

Height of connection plate 400 mm

SPECIFICAȚII

Product Type: Cabinet Door

Material: Oțel

Table 1/2

Număr de catalog	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-358	47U	2200mm	600mm	IP55	1	Black Grey
21630-359	47U	2200mm	800mm	IP55	1	Black Grey
21630-354	38U	1800mm	600mm	IP55	1	Black Grey
21630-356	42U	2000mm	600mm	IP55	1	Black Grey
21630-355	38U	1800mm	800mm	IP55	1	Black Grey
21630-357	42U	2000mm	800mm	IP55	1	Black Grey

Table 2/2

Număr de catalog	Color Code	Finish	Quick Ship
21630-358	RAL 7021	Vopsit Pulbere	No
21630-359	RAL 7021	Vopsit Pulbere	No
21630-354	RAL 7021	Vopsit Pulbere	No
21630-356	RAL 7021	Vopsit Pulbere	No
21630-355	RAL 7021	Vopsit Pulbere	No
21630-357	RAL 7021	Vopsit Pulbere	No

DETALII SUPLIMENTARE DESPRE PRODUS

The height of the rear panel is 400 mm less than the cabinet height to accomodate the connecting plate.

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE