

Varistar CP Cross Member



Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 800 kg static load. The hole pattern allows easy reccessment of the 19" plane in 25 mm increments.

CARACTERISTICI

Side crossbar to support 19" uprights in a 800 mm wide cabinet supporting 800 kg static load

Hole pattern allows easy reccessment of the 19" plane in 25 mm increments

SPECIFICAȚII

Table 1/2

Număr de catalog	Works With	Material	Finish	Color	Color Code	Depth
24630-214	Varistar CP	Oțel	Vopsit Pulbere	Black Grey	RAL 7021	900mm
24630-212	Varistar CP	Oțel	Vopsit Pulbere	Black Grey	RAL 7021	600mm
24630-213	Varistar CP	Oțel	Vopsit Pulbere	Black Grey	RAL 7021	800mm

Table 2/2

Număr de catalog	Package Quantity	Package Unit	Quick Ship
24630-214	4	Pair	No
24630-212	4	Pair	No
24630-213	4	Pair	No

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE