

Varistar CP Deco Frame for 800W Cabinet



The deco frame is a perfect fit for the Varistar CP in 800mm width without a front door. It conceals any cabling on the sides of the cabinet, streamlining cable routing and equipment mounting for a more efficient installation process and simultaneously improving the cabinet's appearance.

CARACTERISTICI

Conceals cabling beside the 19" panel mount, streamlining cable routing and equipment mounting for a more efficient installation process

Provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs

Imparts improved functionality, appearance, and durability for Varistar CP cabinets without a door

SPECIFICAȚII

Product Type: Cabinet/Rack Frame

Material: Oțel

Table 1/2

Număr de catalog	Rack Height	Height	Width	Design Feature	Package Quantity	Color Code
21630-920	47U	2200mm	800mm	Swing frame	1	RAL 7021
21630-926	47U	2200mm	800mm	19" Slide Mounts	1	RAL 7021
21630-918	38U	1800mm	800mm	Swing frame	1	RAL 7021
21630-925	42U	2000mm	800mm	19" Slide Mounts	1	RAL 7021
21630-919	42U	2000mm	800mm	Swing frame	1	RAL 7021

Număr de catalog	Rack Height	Height	Width	Design Feature	Package Quantity	Color Code
21630-924	38U	1800mm	800mm	19" Slide Mounts	1	RAL 7021

Table 2/2

Număr de catalog	Finish	Type	Quick Ship
21630-920	Vopsit Pulbere	Deco Frame	No
21630-926	Vopsit Pulbere	Deco Frame	No
21630-918	Vopsit Pulbere	Deco Frame	No
21630-925	Vopsit Pulbere	Deco Frame	No
21630-919	Vopsit Pulbere	Deco Frame	No
21630-924	Vopsit Pulbere	Deco Frame	No

DETALII SUPLIMENTARE DESPRE PRODUS

The deco frame provides easier access to the cabinet's internal components with hinged or removable panels, simplifying maintenance or repairs. It's an essential addition to any electronics cabinet without a front door, particularly for Automated Test Equipment, providing improved functionality, appearance, and durability.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE