

Varistar CP Raised Top Cover

Fan top cover for better ventilation and active cooling.



CARACTERISTICI

Uses same lifting eyes as normal top cover

SPECIFICAȚII

Product Type: Cabinet/Rack Top Cover

Protection Rating: IP20

Material: Oțel

Table 1/2

Număr de catalog	Width	Depth	Package Quantity	Color	Color Code	Finish
21630-583	600mm	300mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-584	600mm	600mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-585	600mm	800mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-586	600mm	900mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-587	600mm	1000mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-588	600mm	1100mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-589	600mm	1200mm	1	Black Grey	RAL 7021	Vopsit Pulbere

Număr de catalog	Width	Depth	Package Quantity	Color	Color Code	Finish
21630-590	800mm	600mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-591	800mm	800mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-592	800mm	900mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-593	800mm	1000mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-594	800mm	1100mm	1	Black Grey	RAL 7021	Vopsit Pulbere
21630-595	800mm	1200mm	1	Black Grey	RAL 7021	Vopsit Pulbere

Table 2/2

Număr de catalog	Quick Ship
21630-583	No
21630-584	No
21630-585	No
21630-586	No
21630-587	No
21630-588	No
21630-589	No
21630-590	No
21630-591	No
21630-592	No
21630-593	No

Număr de catalog	Quick Ship
21630-594	No
21630-595	No

DETALII SUPLIMENTARE DESPRE PRODUS

Please purchase the grounding kit separately.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE