

VPX System, Desktop, 4 U, 5 Slot, Pluggable PSU



TVPX desktop case for 5 VPX boards 3 U, 160 mm. With or without Rear I/O option The power for the system is supplied by a pluggable open frame power supply.

CERTIFICATIONS



CARACTERISTICI

Backplane conforms to VITA 46 Other VPX backplanes on request System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with VITA 1.1-1994

PSU pluggable, 300 W, 3 U, 8 HP (further PSU optional)

VPX backplane, in accordance with VITA 46, 5 slot, 3 U, 0.8" pitch, full mesh topology

Heat dissipation by 2 radial fans , front to rear side cooling

SPECIFICAȚII

Table 1/3

Număr de catalog	Product Type	Number of Slots	Type	Backplane Type	Data Transfer	Power per Slot
20836-447	System	5	Desktop	VPX Full Mesh	10 GbE	30W
20836-444	System	5	Desktop	VPX Full Mesh	10 GbE	30W

Table 2/3

Număr de catalog	Input Voltage AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
20836-447	100 – 240V	Front to Rear	4U	(1) Pluggable PSU	Yes	Yes
20836-444	100 – 240V	Front to Rear	4U	(1) Pluggable PSU	Yes	No

Table 3/3

Număr de catalog	Complies With	Depth	Height	Package Quantity	Quick Ship
20836-447	ANSI/VITA 46.0-2019	275mm	177mm	1	No
20836-444	ANSI/VITA 46.0-2019	275mm	177mm	1	No

DETALII SUPLIMENTARE DESPRE PRODUS

Modified systems available on request.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Portofoliul nostru puternic de mărci:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE