

# 2-2 Hole Corner Angle Bracket



## FEATURES

Used to create metal frames with nVent CADDY Eristrut channels

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material                        | Finish             | Hole Size (HS) | Thickness (T) | A      |
|----------------|----------------|---------------------------------|--------------------|----------------|---------------|--------|
| ZWA205S6       | 388761         | Stainless Steel 316 (EN 1.4401) |                    | 14 mm          | 6 mm          | 102 mm |
| ZW205          | 313380         | Сталь                           | Hot-Dip Galvanized | 14 mm          | 6 mm          | 102 mm |
| ZWA205EG       | 387652         | Сталь                           | Electrogalvanized  | 14 mm          | 6 mm          | 100 mm |
| ZWA205         | 387650         | Сталь                           | Hot-Dip Galvanized | 14 mm          | 6 mm          | 102 mm |

Table 2/2

| Catalog Number | Article Number | B     | Screw Included | Screw Diameter (Sc) | Screw Length (L) |
|----------------|----------------|-------|----------------|---------------------|------------------|
| ZWA205S6       | 388761         | 86 mm | Нет            |                     |                  |
| ZW205          | 313380         | 86 mm | Да             | 10 mm               | 25mm             |

| Catalog Number | Article Number | B     | Screw Included | Screw Diameter (Sc) | Screw Length (L) |
|----------------|----------------|-------|----------------|---------------------|------------------|
| ZWA205EG       | 387652         | 95 mm | Her            |                     |                  |
| ZWA205         | 387650         | 86 mm | Her            |                     |                  |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

