


# 3000 Beam Clamp Kit



## FEATURES

Medium duty system

Includes clamp and U channel

## SPECIFICATIONS

**Finish:** Electrogalvanized

**Material:** Сталь

Table 1/2

| Catalog Number | Article Number | Длина мм (L) | Height (H) | Width (W) | Thickness (T) | Flange Thickness (FT) |
|----------------|----------------|--------------|------------|-----------|---------------|-----------------------|
| 3300EG         | 570410         | 300mm        | 15 mm      | 30 mm     | 2.5 mm        | 15 mm Max             |
| 3400EG         | 570420         | 400mm        | 15 mm      | 30 mm     | 2.5 mm        | 15 mm Max             |
| 3500EG         | 570430         | 500mm        | 15 mm      | 30 mm     | 2.5 mm        | 15 mm Max             |
| 3600EG         | 570440         | 600mm        | 15 mm      | 30 mm     | 2.5 mm        | 15 mm Max             |

Table 2/2

| Catalog Number | Article Number | Hole Size (HS) | Static Load 1 (F1) | Static Load 2 (F2) | Static Load 3 (F3) |
|----------------|----------------|----------------|--------------------|--------------------|--------------------|
| 3300EG         | 570410         | 13 mm          | 3700N              | 490N               | 390N               |

| Catalog Number | Article Number | Hole Size (HS) | Static Load 1 (F1) | Static Load 2 (F2) | Static Load 3 (F3) |
|----------------|----------------|----------------|--------------------|--------------------|--------------------|
| 3400EG         | 570420         | 13 mm          | 3700N              | 490N               | 390N               |
| 3500EG         | 570430         | 13 mm          | 3700N              | 490N               | 390N               |
| 3600EG         | 570440         | 13 mm          | 3700N              | 490N               | 390N               |

**Screw Diameter (Sc):** 8

**X:** 10.5 x 25 mm

**D:** 25 mm

**Torque (TQ):** 30 N·m

**E:** 31.5 mm

**A:** 40 mm

**B:** 100 mm

**C:** 150 mm

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

