

# **nVent CADDY Rod Lock Anchor Screw**



## **CERTIFICATIONS**





### **FEATURES**

For use with concrete and solid brick

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Works with slightly damaged threads and minor burrs on the threaded rod

## **SPECIFICATIONS**


Finish: Electrogalvanized


Material: Сталь

Table 1/2								
Catalog Number	Article Number	Rod Size (RS)	В	С	Длина мм (L)	Drill Bit Diameter		
CRLAM8EG	390009	8	32 mm	22 mm	72mm	8mm		
CRLAM10EG	390010	10	32 mm	22 mm	72mm	8mm		

Table 2/2							
Catalog Number	Article Number	<b>Drill Hole Depth</b>	Static Load	Certifications			
CRLAM8EG	390009	50mm	2900N	ITB			
CRLAM10EG	390010	50mm	2900N	FM Approved, Pipe Hanger Components, ITB			

## **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

# Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

ILSCO

**SCHROFF** 

**TRACHTE** 

