

nVent CADDY Speed Link SLK with Hammer-On Flange Clip



CERTIFICATIONS





FEATURES

Complete system includes wire, locking device and pre-assembled nVent CADDY Hammer-On Flange Clip end fitting

Installs with just a hammer

Fits most beams

SPECIFICATIONS

Static Load Safety Factor: 5:1

Finish: Electrogalvanized


Complies With: SMACNA HVAC-DCS

Table 1/1									
Catalog Number	Article Number	Material	Wire Rope Diameter	Wire Rope Length	Flange Thickness (FT)	Static Load			
SLK2L34H24	196535	Steel, Polypropylene, Zinc Alloy	2 mm	3m	3 - 8 mm	440N			

CatalogNumber	Article Number	Material	Wire Rope Diameter	Wire Rope Length	Flange Thickness (FT)	Static Load
SLK15L34H24	196506	Steel, Polypropylene, Zinc Alloy	1.5 mm	3m	3 - 8 mm	195N
SLK15L34H58	196507	Steel, Polypropylene, Zinc Alloy	1.5 mm	3m	8 - 14 mm	195N
SLK2L34H58	196536	Steel, Polypropylene, Zinc Alloy	2 mm	3m	8 - 14 mm	440N

Thickness (T): 12.5 mm Width (W): 19 mm Height (H): 55 mm Angle (a): 90 ° Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

