

# 19-дюймовый кабельный ввод

## Data Solutions

19-дюймовый блок для удобной и эффективной организации кабелей (кабельный ввод).



### CERTIFICATIONS



### FEATURES

19-дюймовая передняя панель для кабельного ввода

### SPECIFICATIONS

**Аксессуар Тип:** Передняя панель

**Product Type:** Передняя панель

**Material:** Сталь

Table 1/3

Catalog Number	Rack Height	Mounting	Package Quantity	Front Finish	Rear Finish	Color Code
20118-734	1U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-767	1U	Screw-on Front	1	Painted	Painted	RAL 7021

CatalogNumber	Rack Height	Mounting	Package Quantity	Front Finish	Rear Finish	Color Code
20118-736	2U	Screw-on Front	1	Painted	Painted	RAL 7035
20118-768	2U	Screw-on Front	1	Anodized	Conductive	RAL 7021

Table 2/3

Catalog Number	Глубина мм	EMC Shielding	Finish	Высота мм	Rack Width	Type
20118-734	1.5mm	Нет	Powder Coated	43.6mm	95HP	19" Front Panel
20118-767	1.5mm	Нет	Powder Coated	43.6mm	95HP	19" Front Panel
20118-736	1.5mm	Нет	Powder Coated	88.1mm	95HP	19" Front Panel
20118-768	1.5mm	Нет	Powder Coated	88.1mm	95HP	19" Front Panel

Table 3/3

Catalog Number	Ширина мм
20118-734	483mm
20118-767	483mm
20118-736	483mm
20118-768	483mm

## ADDITIONAL PRODUCT DETAILS

Монтажный комплект для сборки на 19 дюймов заказывается отдельно.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**