

19-дюймовая полка для оборудования, регулируемая глубина

Data Solutions



19-дюймовые полки для оборудования Schroff с максимальной нагрузкой до 10 кг позволяют компактно располагать оборудование в шкафу.

CERTIFICATIONS



FEATURES

Глубина регулируется с шагом 25 мм., выступ спереди мин. 26 мм

Монтажная высота 2 U

Допустимая статическая нагрузка 15 кг

SPECIFICATIONS

Product Type: Полка с креплением на каркасе

Material: Сталь

Table 1/2

Catalog Number	Ширина мм	Глубина мм	Package Quantity	Color	Color Code	Finish
20118-786	430mm	250mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Ширина мм	Глубина мм	Package Quantity	Color	Color Code	Finish
20118-791	430mm	400mm	1	Light Grey	RAL 7035	Powder Coated
20118-790	430mm	300mm	1	Light Grey	RAL 7035	Powder Coated
20118-789	430mm	250mm	1	Light Grey	RAL 7035	Powder Coated
20118-788	430mm	400mm	1	Black Grey	RAL 7021	Powder Coated
20118-787	430mm	300mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Type
20118-786	Equipment Shelf
20118-791	Equipment Shelf
20118-790	Equipment Shelf
20118-789	Equipment Shelf
20118-788	Equipment Shelf
20118-787	Equipment Shelf

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE