

Cable to Ground Rod Splice/Grounding Receptacle, GB/GR, 3/4" dia, 1/0 Concentric, B165

Data Solutions

CATALOG NUMBER

GBJGR182CR1



nVent ERICO Cadweld graphite molds are designed and engineered for thousands of connection styles and conductor combinations.

CERTIFICATIONS



FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

PRODUCT ATTRIBUTES

Ground Rod Type: Copper-bonded
Mold Family: GB/GR Mold Family
Ground Rod Diameter, Nominal: 0.75in
Ground Rod Diameter, Actual (Ø): 17.32mm
Conductor Size: 1/0 Concentric
Conductor Outer Diameter, Nominal: 9.47mm
Ground Plate/Grounding Receptacle: B165 Grounding Receptacle
Mold Split: Vertical
Split Crucible: Het
Wear Plates: Het
Mold Only: Het
Welding Material: 200 x 2 or 400PLUSF20, Sold Separately
Handle Clamp: L159, Sold Separately
Frame: Attached
Price Key: J
Ease of Use: Preferred

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A gap between conductors may be required. See mold tag for more information.

XX-X-XX-XX-XX-XX-L-M-W		
XX	Mold Family	
X	Price Key	
XX	Mold Family	
XX	Ground Rod Type	
XX	Conductor Code	
XX	Grounding Receptacle	
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning
M*	Mold Only	
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points

* Empty if none

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE