

Low Voltage Insulators, Metric Thread, 15 mm, 14 mm Hex Width, M4 Thread

Data Solutions

CATALOG NUMBER

ISOTP15M4



CERTIFICATIONS



FEATURES

Halogen free

High resistance to leakage current

Great stability of electrical and mechanical parameters

Fiberglass reinforced

UL® Recognized in E125470 and evaluated for dielectric withstand rating of 1,500 VAC/DC

RoHS compliant

PRODUCT ATTRIBUTES

Article Number: 548400

Material: Сталь; Glass Fibre Reinforced Polyamide

Finish: Electrogalvanized

Working Temperature: -40 to 130°C

Flammability Rating: UL® 94V-0

Complies With: IEC® 60695-2-11 (Glow Wire Test 960 °C)

Dielectric Strength, IEC 61439.1: 2500 VAC @ 1 min

Dielectric Strength, UL: 1500

Insulation Voltage: 500; 500

Height (H): 15mm

Hex Width (W): 14mm

Глубина мм (D): 16mm

Thread Size (TS): M4

Thread Depth (TD): 4mm

Diameter (Ø): 12mm

Static Load 1 (F1): 150daN


Static Load 2 (F2): 100daN

Unit Weight: 0.01kg

ADDITIONAL PRODUCT DETAILS

Creepage and clearance distances need to be in accordance with the relevant application standard.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE