

# Стальная дверь Varistar CP, перфорированная, с 3-точечным запиранием, RAL 7021, 47 U, высота 2200, ширина 600

## Data Solutions

### CATALOG NUMBER

**21630-099**



Перфорированная стальная дверь Varistar CP с трехточечным запиранием для обеспечения класса защиты IP 20.

### FEATURES

Перфорированная стальная дверь с 3-точечным запиранием для обеспечения класса защиты IP 20

Поворотная ручка с кнопкой

Угол открытия 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### PRODUCT ATTRIBUTES

Rack Height: 47U

Высота мм: 2200mm

Ширина мм: 600mm

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1; IEC 61587-3

Finish: Powder Coated

Locking Type: 3-Point Locking

Material: Сталь

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Steel Door, Perforated

Works With: Varistar CP

## ADDITIONAL PRODUCT DETAILS

---

Профильный DIN-получилиндр для поворотной ручки заказывается отдельно

Комплект заземления можно приобрести отдельно.

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE