

Стальная дверь Varistar CP, сплошная, с 3-точечным запирающим, RAL 7021, 24 U, высота 1200, ширина 600, IP55

Data Solutions

CATALOG NUMBER

21630-210



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

PRODUCT ATTRIBUTES

Rack Height: 24U

Высота мм: 1200mm

Ширина мм: 600mm

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1

Finish: Powder Coated

Locking Type: 3-Point Locking

Material: Сталь

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP55

Type: Steel Door

Works With: Varistar CP

Net Weight: 13.509kg

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE