

Стальная дверь Varistar CP, перфорированная, с 1-точечным запиранием, RAL 7021, 24 U, высота 1200, ширина 800

Data Solutions

CATALOG NUMBER

21630-409



Перфорированная стальная дверь Varistar CP с
одноточечным запиранием для областей применения,
соответствующих стандарту IP 20.

FEATURES

Перфорированная стальная дверь с одноточечным запиранием для обеспечения класса защиты IP 20

Поворотная ручка с кнопкой

Угол открытия 180°

Замочная накладка

Замочная накладка

PRODUCT ATTRIBUTES

Rack Height: 24U

Высота мм: 1200mm

Ширина мм: 800mm

Locking Type: Single Point Locking

Package Quantity: 1

Color: Black Grey

Color Code: RAL 7021

Complies With: IEC 61587-1; IEC 61587-3

Material: Сталь

Product Family: Varistar CP

Product Type: Cabinet Door

Protection Rating: IP20

Type: Steel Door, Perforated

Works With: Varistar CP

Net Weight: 11.316kg

ADDITIONAL PRODUCT DETAILS

Поворотная ручка и полуцилиндр с DIN-профилем заказываются отдельно.

Комплект заземления можно приобрести отдельно.

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE