

Basic PDU, EB0337, 230 VAC, 1-PH, 32 A

Data Solutions

CATALOG NUMBER

EB0337



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Панели электропитания

Socket Type: (36) C13; (6) C19

Socket Quantity: 42

Color: Черный

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: Нет

Circuit Breaker Quantity: 2

Power Rating: 5 kVA North America; 7.4 kVA International

Input Cable Location: Top Feed

Input Voltage: 200 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 7.44 kVA

Nominal Voltage: 230V

On/Off Switch Included: Нет

Output Voltage: 230VAC

Amperage (Derated Amperage): 30 A (24 A) North America; 32 A International

Plug Type: IEC 60309 332P6 (IP44)

Rack Units: 0U

Removable Input Cable: Нет

Metering Type: Нет

Material: Сталь

Finish: Powder Coated

Высота мм: 1490mm

Ширина мм: 52mm

Глубина мм: 53mm

Weight: 7.21kg

Package Quantity: 1

Input Cable Length: 3m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE