

Саморегулирующиеся греющие кабели IceStop

Data Solutions



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

FEATURES

Простая конструкция

GM-2XT для крыш с битумным покрытием

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

SPECIFICATIONS

Nominal Thickness:	6mm
Nominal Width:	14mm
Nominal Cable Weight:	130g/m
Supply Voltage:	208 – 240V
Min Installation Temperature:	-18°C
Color:	Черный
Ground Path Type:	Braid
Conductor Material:	Nickel-Plated Copper

Table 1/1

Catalog Number	Article Number	Nominal Power Output, In Air @ 0°C, 230V	Nominal Power Output, In Ice Water @ 0°C, 230V	Outer Jacket Material
092961-000	GM-2XT	18W/m	36W/m	Fluoropolymer
446105-000	GM-2X	18W/m	36W/m	Modified Polyolefin

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE