

Intelligent PDU, EN2xxx, 230 VAC, 1-PH

Data Solutions

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FEATURES

Enlogic EN2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/6

| Catalog Number | Product Family | Type | Product Type | Socket Type | Socket Quantity | Color |
|----------------|----------------|----------------------|-----------------------|-------------------|-----------------|--------|
| EN2326 | Enlogic | Интеллектуальные PDU | Панели электропитания | (20) C13, (4) C19 | 24 | Черный |
| EN2316-A | Enlogic | Интеллектуальные PDU | Панели электропитания | (12) C13, (4) C19 | 16 | Черный |
| EN2317 | Enlogic | Интеллектуальные PDU | Панели электропитания | (12) C13, (4) C19 | 16 | Черный |
| EN2325 | Enlogic | Интеллектуальные PDU | Панели электропитания | (20) C13, (4) C19 | 24 | Черный |

| CatalogNumber | Product Family | Type | Product Type | Socket Type | SocketQuantity | Color |
|---------------|----------------|--------------------------|------------------------------|---|----------------|--------|
| EN2329 | Enlogic | Интеллектуаль ные PDU | Панели электропитани я | (24) C13, (8) C19 | 32 | Черный |
| EN2350 | Enlogic | Интеллектуаль ные PDU | Панели электропитани я | (20) C13/C15, (20) C13/C15/C19/C 21 | 40 | Черный |
| EN2380 | Enlogic | Интеллектуаль ные PDU | Панели электропитани я | (16) Locking C13/C15, (16) Locking C13/C15/C19/C 21 | 32 | Черный |
| EN2337 | Enlogic | Интеллектуаль ные PDU | Панели электропитани я | (38) C13, (6) C19 | 44 | Черный |

Table 2/6

| Catalog Number | Circuit Breaker | Switched Outlets | Circuit Breaker Quantity | Power Rating | Input Cable Length | Input Cable Location |
|----------------|----------------------|------------------|--------------------------|--------------|--------------------|----------------------|
| EN2326 | No Circuit Breaker | Да | 0 | 3.7 kVA | 3m | Top Feed |
| EN2316-A | 16 A, 1-pole, Hy-Mag | Да | 0 | | | Front Feed |
| EN2317 | 16 A, 1-pole, Hy-Mag | Да | 0 | | | Top Feed |
| EN2325 | 16 A, 1-pole, Hy-Mag | Да | 2 | 7.4 kVA | 3m | Top Feed |
| EN2329 | 16 A, 1-pole, Hy-Mag | Да | 2 | 7.4 kVA | 3m | Top Feed |
| EN2350 | 20 A, 1-pole, Hy-Mag | Да | 2 | 7.4 kVA | 3m | Top Feed |
| EN2380 | 20 A, 1-pole, Hy-Mag | Да | 2 | 7.4 kVA | 3m | Top Feed |
| EN2337 | 16 A, 1-pole, Hy-Mag | Да | 2 | | | Top Feed |

Table 3/6

| Catalog Number | Input Voltage | Phase | Max Power Input | Nominal Voltage | On/Off Switch Included | Output Voltage |
|----------------|---------------|-------|-----------------|-----------------|------------------------|----------------|
| EN2326 | 100 – 240V | 1 PH | 3.68 kVA | 230V | Да | 230VAC |

| CatalogNumber | Input Voltage | Phase | Max Power Input | Nominal Voltage | On/Off Switch Included | Output Voltage |
|---------------|---------------|-------|-----------------|-----------------|------------------------|----------------|
| EN2316-A | 100 – 240V | 1 PH | 3.68 kVA | | | 100 – 240VAC |
| EN2317 | 200 – 240V | 1 PH | 3.68 kVA | | | 200 – 240VAC |
| EN2325 | 200 – 240V | 1 PH | 7.44 kVA | 230V | Да | 230VAC |
| EN2329 | 200 – 240V | 1 PH | 7.44 kVA | 230V | Да | 230VAC |
| EN2350 | 200 – 240V | 1 PH | 7.44 kVA | 230V | Да | 230VAC |
| EN2380 | 200 – 240V | 1 PH | 7.44 kVA | 230V | Да | 230VAC |
| EN2337 | 200 – 240V | 1 PH | 7.44 kVA | | | 200 – 240VAC |

Table 4/6

| Catalog Number | Amperage (Derated Amperage) | Plug Type | Rack Units | Removable Input Cable | Metering Type | Material |
|----------------|--|------------------------|------------|-----------------------|---------------|----------|
| EN2326 | 16 A | IEC 60309 316P6 (IP44) | 0U | Да | Input | Сталь |
| EN2316-A | 20 A (16 A) North America, 16 A International | C20 | 0U | Да | Input | |
| EN2317 | 16 A | IEC 60309 316P6 (IP44) | 0U | Нет | Input | |
| EN2325 | 32 A | IEC 60309 332P6 (IP44) | 0U | Нет | Input | Сталь |
| EN2329 | 32 A | IEC 60309 332P6 (IP44) | 0U | Нет | Input | Сталь |
| EN2350 | 32 A | IEC 60309 332P6 (IP44) | 0U | Нет | Input | Сталь |
| EN2380 | 32 A | IEC 60309 332P6 (IP44) | 0U | Нет | Input | Сталь |
| EN2337 | 32 A | IEC 60309 332P6 (IP44) | 0U | Нет | Input | |

Table 5/6

| Catalog Number | Finish | Высота мм | Ширина мм | Глубина мм | Weight | Package Quantity |
|----------------|---------------|-----------|-----------|------------|--------|------------------|
| EN2326 | Powder Coated | 1490mm | 52mm | 53mm | 7.21kg | 1 |
| EN2316-A | | | | | | 1 |
| EN2317 | | | | | | 1 |
| EN2325 | Powder Coated | 1750mm | 52mm | 53mm | 9.5kg | 1 |
| EN2329 | Powder Coated | 1750mm | 52mm | 53mm | 8.52kg | 1 |
| EN2350 | Powder Coated | 1490mm | 56mm | 75mm | 9.12kg | 1 |
| EN2380 | Powder Coated | 1490mm | 56mm | 75mm | | 1 |
| EN2337 | | | | | | 1 |

Table 6/6

| Catalog Number | Interrupt Rating |
|----------------|------------------|
| EN2326 | 5kAIC |
| EN2316-A | 5kAIC |
| EN2317 | 5kAIC |
| EN2325 | 5kAIC |
| EN2329 | 5kAIC |
| EN2350 | 5kAIC |
| EN2380 | 5kAIC |
| EN2337 | 5kAIC |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE