

Intelligent PDU, EN5xxx, 400 VAC, 3-PH

Data Solutions



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

FEATURES

Enlogic EN5xxx Intelligent Power Distribution Units monitors input power of the entire PDU and individual outlet monitoring, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN5402	Enlogic	Интеллектуальные PDU	Панели электропитания	(18) C13, (6) C19	24	Черный
EN5808	Enlogic	Интеллектуальные PDU	Панели электропитания	(12) C13, (12) C19	24	Черный
EN5810	Enlogic	Интеллектуальные PDU	Панели электропитания	(24) C13, (12) C19	36	Черный

CatalogNumber	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EN5850	Enlogic	Интеллектуаль ные PDU	Панели электропитани я	(24) C13/C15, (24) C13/C15/C19/C 21	48	Черный
EN5812	Enlogic	Интеллектуаль ные PDU	Панели электропитани я	(36) C13, (12) C19	48	Черный

Table 2/6

Catalog Number	Switched Outlets	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Input Cable Location	Input Voltage
EN5402	Нет	No Circuit Breaker	11.0 kVA	0	Top Feed	380 – 415V
EN5808	Нет	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5810	Нет	16 A, 1-pole, Hy-Mag	22.0 kVA	6	Top Feed	380 – 415V
EN5850	Нет	20 A, 1-pole, Hy-Mag	17.3 kVA North America, 22.1 kVA International	6	Top Feed	380 – 415V
EN5812	Нет	16 A, 1-pole, Hy-Mag		6	Top Feed	400V

Table 3/6

Catalog Number	Phase	Interrupt Rating	Nominal Voltage	Max Power Input	On/Off Switch Included	Amperage (Derated Amperage)
EN5402	3 PH		415V	11.0 kVA	Нет	16 A
EN5808	3 PH		415V	22.0 kVA	Нет	32 A
EN5810	3 PH		415V	22.0 kVA	Нет	32 A
EN5850	3 PH		415V	17.3 / 22.1 kVA	Нет	30 A (24 A) North America, 32 A International
EN5812	3 PH WYE	5kAIC		22.0 kVA		32 A

Table 4/6

Catalog Number	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material
EN5402	230VAC	0U	IEC 60309 516P6 (IP44)	Outlet	Нет	Сталь
EN5808	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	Да	Сталь
EN5810	230VAC	0U	IEC 60309 532P6 (IP44)	Outlet	Нет	Сталь
EN5850	208 – 230VAC	0U	IEC 60309 530P6/532P6	Outlet	Нет	Сталь
EN5812	200 – 240VAC	0U	IEC 60309 532P6 (IP44)	Outlet	Нет	

Table 5/6

Catalog Number	Finish	Высота мм	Ширина мм	Глубина мм	Weight	Package Quantity
EN5402	Powder Coated	1780mm	52mm	53mm	7.82kg	1
EN5808	Powder Coated	1780mm	52mm	53mm		1
EN5810	Powder Coated	1780mm	85mm	53mm	12.23kg	1
EN5850	Powder Coated	1780mm	56mm	75mm	11.93kg	1
EN5812						1

Table 6/6

Catalog Number	Input Cable Length
EN5402	3m
EN5808	3m
EN5810	3m
EN5850	1.8m
EN5812	

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE