

LED Lights for Cabinets

Data Solutions



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



FEATURES

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

SPECIFICATIONS

Product Type: Light

Table 1/3

Catalog Number	Input Voltage AC	Аксессуар Тип	Input Voltage DC	Длина мм	Package Quantity	Color
57274	250V max	Светильник			1	Черный
57275		Светильник			2	Черный

CatalogNumber	Input Voltage AC	Аксессуар Тип	Input Voltage DC	Длина мм	Package Quantity	Color
57265	230V max	Светильник	24V max	396mm	1	Черный
57272	250V max	Светильник		3000mm	1	Черный
57273	250V max	Светильник		1000mm	1	Черный

Table 2/3

Catalog Number	Глубина мм	Finish	Высота мм	Material	Type	Ширина мм
57274	14mm	Smooth Matte	53mm	Plastic	Cabinet Light, Клеммный блок	18mm
57275	4mm	Smooth Matte	30mm		Cabinet Light, Magnet	12mm
57265	40mm	Smooth Matte		Plastic	Cabinet Light	33mm
57272		Smooth Matte		Plastic	Connection Cable	0.3mm
57273		Smooth Matte		Plastic	Cabinet Light	

Table 3/3

Catalog Number	Color Temperature	Nominal Voltage	Operating Temperature	Weight	Certifications
57274		250V	60°C min	0.07kg	
57275				0.08kg	
57265	5800K	230V	-20 to 55°C	0.24kg	RoHS, CE
57272		250V	60°C min		
57273		250V	60°C min	0.3kg	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE