

# Монитор, Клавиатура, сенсорная панель, Ящик 1 U, Уменьшенная глубина

## Data Solutions



Designed for standard 19" rackmount designed for comfort  
robust design for heavy use or harsh environment operation

## CERTIFICATIONS



## FEATURES

Выдвижное шасси для 17-дюймового цветного TFT-монитора, 1 U (разрешение Full HD; подключается к интерфейсу VGA или DVI-D)

Клавиатура с другой раскладкой (подключается через USB)

Встроенная сенсорная панель (подключается через USB)

Напряжение питания: Широкополосный вход (номинальное напряжение сети от 110 до 240 В перем. тока), напряжение питания 12, 24 и 48 В пост. тока – по запросу

Регулируемая глубина крепления с разным шагом серверной панели/монтажного профиля; Глубина монтажа (размер с = интервал 19-дюймового профиля): размер с 450 ... 640 мм

С соединением DVI

## SPECIFICATIONS

**Глубина мм:** 400mm

**Product Type:** Cabinet/Rack Drawer

Table 1/1

Catalog Number	Rack Height	Color	Color Code	Type	Works With	Keyboard Type
60118-583	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	QWERTY UK
60118-584	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	QWERTZ
60118-585	1U	Jet Black	RAL 9005	Monitor, Keyboard, Touchpad	19" Cabinets	AZERTY

## ADDITIONAL PRODUCT DETAILS

Дополнительные версии по запросу – с трекболом или цифровым планшетом.

Другие раскладки клавиатуры см. в руководстве пользователя.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**