

Secure Dual W-Lock Power Cord

Data Solutions



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

FEATURES

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Works With	Длина мм	Color	Высота мм	Input Cable Length
EP1314024X150	Cable	RackPower	600mm	Черный	270mm	588m
EP1314048X125	Cable	RackPower	1200mm	Черный	270mm	1.176m
EP1314072X100	Cable	RackPower	1800mm	Черный	270mm	1.764m
EP1314B24X150	Cable	RackPower	600mm	Blue	270mm	0.588m
EP1314B48X125	Cable	RackPower	1200mm	Blue	270mm	1.176m

CatalogNumber	Type	Works With	Длина мм	Color	Высота мм	Input Cable Length
EP1314B72X100	Cable	RackPower	1800mm	Blue	270mm	1.764m
EP1314R24X150	Cable	RackPower	600mm	Красный	270mm	0.588m
EP1314R48X125	Cable	RackPower	1200mm	Красный	270mm	1.176m
EP1314R72X100	Cable	RackPower	1800mm	Красный	270mm	1.764m
EP1920024X100	Cable	RackPower	600mm	Черный	270mm	0.588m
EP1920048X75	Cable	RackPower	1200mm	Черный	270mm	1.176m
EP1920072X50	Cable	RackPower	1800mm	Черный	270mm	1.764m
EP1920B24X100	Cable	RackPower	600mm	Blue	270mm	0.588m
EP1920B48X75	Cable	RackPower	1200mm	Blue	270mm	1.176m
EP1920B72X50	Cable	RackPower	1800mm	Blue	270mm	1.764m
EP1920R24X100	Cable	RackPower	600mm	Красный	270mm	0.588m
EP1920R48X75	Cable	RackPower	1200mm	Красный	270mm	1.176m
EP1920R72X50	Cable	RackPower	1800mm	Красный	270mm	1.764m

Table 2/2

Catalog Number	Package Quantity	Plug Type	Removable Input Cable
EP1314024X150	150	C13/C14	Нет

Catalog Number	Package Quantity	Plug Type	Removable Input Cable
EP1314048X125	125	C13/C14	Нет
EP1314072X100	100	C13/C14	Нет
EP1314B24X150	150	C13/C14	Нет
EP1314B48X125	125	C13/C14	Нет
EP1314B72X100	100	C13/C14	Нет
EP1314R24X150	150	C13/C14	Нет
EP1314R48X125	125	C13/C14	Нет
EP1314R72X100	100	C13/C14	Нет
EP1920024X100	100	C19/C20	Нет
EP1920048X75	75	C19/C20	Нет
EP1920072X50	50	C19/C20	Нет
EP1920B24X100	100	C19/C20	Нет
EP1920B48X75	75	C19/C20	Нет
EP1920B72X50	50	C19/C20	Нет
EP1920R24X100	100	C19/C20	Нет
EP1920R48X75	75	C19/C20	Нет
EP1920R72X50	50	C19/C20	Нет

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE