

# Блок розеток, IEC C13, со встроенным измерением мощности

## Data Solutions



Блок распределения питания со встроенным измерением мощности. Полученные данные о мощности отображаются на встроенном дисплее.

### CERTIFICATIONS



### FEATURES

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

Монтажная высота 1 U

Встроенная функция измерения и отображение на локальном дисплее

Панель электропитания с розетками IEC 60320-C13

Возможен горизонтальный и вертикальный монтаж

### SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type          | Socket Type | Socket Quantity | Color | Switched Outlets | Длина мм |
|----------------|-----------------------|-------------|-----------------|-------|------------------|----------|
| 60110-296      | Панели электропитания | IEC C13     | 8               | Серый | Да               | 438.5mm  |

Table 2/2

| Catalog Number | Voltage AC | Глубина мм | Material            | Package Quantity |
|----------------|------------|------------|---------------------|------------------|
| 60110-296      | 230V       | 44mm       | Алюминий, Polyamide | 1                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE