

# панель электропитания, IEC C13, с входом Wieland®

## Data Solutions



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Эта панель электропитания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф. Разъем Wieland обеспечивает простую комбинацию с различными входными кабелями питания.

### CERTIFICATIONS



### FEATURES

Вход: штекер Wieland® GST 18

Установочная высота 1 U

В соответствии с IEC 60320

Горизонтальная или вертикальная установка

Выходы: розетки IEC 60320 C-13

Во время установки панель электропитания можно поворачивать во всех направлениях (с шагом 90°)

### SPECIFICATIONS

|                      |                       |
|----------------------|-----------------------|
| <b>Длина мм:</b>     | 438.5mm               |
| <b>Material:</b>     | Алюминий; Polyamide   |
| <b>Product Type:</b> | Панели электропитания |

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Function               | Package Quantity |
|----------------|-------------|-----------------|------------------|------------|------------------------|------------------|
| 60110-340      | IEC C13     | 12              | Нет              | 230V       |                        | 1                |
| 60110-341      | IEC C13     | 12              | Нет              | 230V       |                        | 1                |
| 60110-342      | IEC C13     | 12              | Нет              | 230V       |                        | 1                |
| 60110-349      | IEC C13     | 6               | Нет              | 230V       | Overcurrent Protection | 1                |
| 60110-350      | IEC C13     | 6               | Нет              | 230V       | Overcurrent Protection | 1                |
| 60110-351      | IEC C13     | 6               | Нет              | 230V       | Overcurrent Protection | 1                |

Table 2/2

| Catalog Number | Color   | Глубина мм | Finish   |
|----------------|---------|------------|----------|
| 60110-340      | Серый   | 44mm       | Anodized |
| 60110-341      | Черный  | 44mm       | Anodized |
| 60110-342      | Красный | 44mm       | Anodized |
| 60110-349      | Серый   | 44mm       | Anodized |
| 60110-350      | Черный  | 44mm       | Anodized |
| 60110-351      | Красный | 44mm       | Anodized |

## ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**