

Блок розеток, UTE, 3-фазный, 9 розеток

Data Solutions



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Распределительный блок питания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф с розетками UTE.

CERTIFICATIONS



FEATURES

Сетевой кабель 2 м, открытый конец с втулочным наконечником

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

Блоки с розетками UTE, 3-фазный

3 фазы, 16 А на фазу

В соответствии с NFC 61-303

Вертикальный монтаж

Установочная высота 1 U

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Color	Switched Outlets	Длина мм
----------------	--------------	-------------	-----------------	-------	------------------	----------

60110-233	Панели электропитания	UTE	9	Серый, Черный, Красный	Нет	608.5mm
-----------	-----------------------	-----	---	------------------------	-----	---------

Table 2/2					
Catalog Number	Voltage AC	Глубина мм	Finish	Material	Package Quantity
60110-233	230V	44mm	Anodized	Алюминий, Polyamide	1

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE