

Датчик температуры, Влажности, Digital Contact Sensor for Guard'an

Data Solutions



Внешний датчик контроля температуры, влажности и мониторинга цифровых входов с 2 разъемами RJ45. До 16 датчиков могут быть последовательно связаны коммутационным кабелем и подключены к одному порту управления Guardian.

FEATURES

Внешний датчик для шлюза Guardian Management Gateway

Один порт шлюза способен отслеживать до 16 сенсорных устройств с общей длиной кабеля 40 м.

Если датчик подключен к nVent SCHROFF Guardian, он отобразится в веб-интерфейсе с указанием типа и серийного номера

Пластмассовый корпус

Простой монтаж

Соединение 2 x RJ 45

Простое подключение по цепочке (daisy-chain) коммутационным кабелем CAT6 (или кабелем с более сильным экранированием)

SPECIFICATIONS

Table 1/1

Catalog Number	Type	Works With	Package Quantity
21070-120	Temperature, Humidity and Digital Contact	Guardian Management Gateway	1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE