

Varistar CP Server Cabinet With Castors

Data Solutions



Сварная стальная рама для высоких динамических нагрузок. Подходит для интеграции 19-дюймового ИТ-оборудования.

FEATURES

Предварительно сконфигурирован, готовый к использованию шкаф

Высокая динамическая нагрузка 1000 кг с интегрированными поворотными роликами, допустимая статическая нагрузка до 1600 кг

Степень защиты IP 20

Возможна установка различного ИТ-оборудования

Встроенные панели для управления воздушными потоками для охлаждения спереди назад

Легко интегрируется в систему изолированного коридора

SPECIFICATIONS

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Cladding Material	Ширина мм	Cladding Color	Глубина мм
----------------	-------------	-----------	-------------------	-----------	----------------	------------

10630-022	42U	2000mm	Сталь	800mm	Black Grey	1200mm
10630-021	42U	2000mm	Сталь	600mm	Black Grey	1200mm

Table 2/2					
Catalog Number	Package Quantity	Dynamic Load	Finish	Material	Type
10630-022	1	1000kgf	Powder Coated	Сталь	Mobile
10630-021	1	1000kgf	Powder Coated	Сталь	Mobile

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE