

Cable to Web of Rail T21 Complete Welder, Signal



FEATURES

Complete right hand or left hand web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 141 lb. rail

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Rail Type: 85 lb to 141 lb T-Rail Sections

Table 1/2								
Catalog Number	Article Number	Material	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style		
SBTBT21YRH		Сталь, Graphite	1" Tab	16 mm ² Concentric	5.18mm	T21		
SBTBT21YLH		Сталь, Graphite	1" Tab	16 mm ² Concentric	5.18mm	T21		
SBTBT21XRH		Сталь, Graphite	1" Tab	25 mm ² Concentric	6.6mm	T21		
SBWT21W6RH	223217	Сталь, Graphite	Field-made	50 mm² Solid	8mm	T21		

CatalogNumber	Article Number	Material	Bond Terminal Style	Conductor Size	Conductor OuterDiameter, Nominal	Welder Style
SBWT21W6LH		Сталь, Graphite	Field-made	50 mm² Solid	8mm	T21

Table 2/2						
Catalog Number	Article Number	Orientation				
SBTBT21YRH		Right Hand				
SBTBT21YLH		Left Hand				
SBTBT21XRH		Right Hand				
SBWT21W6RH	223217	Right Hand				
SBWT21W6LH		Left Hand				

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE