

Ground Rod Socket Driving Stud for Externally Threaded Ground Rods



FEATURES

Used in conjunction with threaded couplers while driving threaded ground rods


SPECIFICATIONS

Material: Сталь

Table 1/1

Catalog Number	Article Number	Ground Rod Diameter, Nominal	Thread Size (TS)	Длина мм (L)	Thread Length (TL)
158100	158100	0.88"	5/8" UNC	47.7mm	31.8mm
158110	158110	1"	3/4" UNC	57.2mm	38.1mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE