

ISOnV Mast Stand



FEATURES

Used to support ISOnV mast assemblies with an outlet

Masts and cables can be assembled horizontally, and stood up into this stand from a level position

SPECIFICATIONS

Material: Stainless Steel 304 (EN 1.4301)

Table 1/1

Catalog Number	Длина мм (L)	Height (H)	Width (W)
ISONVSTAND10	1240mm	600 mm	860 mm
ISONVSTAND15	1730mm	900 mm	1205 mm
ISONVSTAND25	2860mm	1450 mm	2005 mm

ADDITIONAL PRODUCT DETAILS

ISOnV Mast Stand must be installed with four concrete block supports.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE