

Non-Insulated Stranded Conductor for Lightning Protection



CERTIFICATIONS



FEATURES

Provides a path to ground for lightning currents

SPECIFICATIONS

Certification Details: UL® 96

Table 1/2

Catalog Number	Material	UL Conductor Class	Conductor Type	Number of Wires	Wire Diameter	Diameter
LPA102500	Алюминий	Class I	Smooth Weave	28	1.63mm	13.46 mm
LPA100500	Алюминий	Class I	Smooth Weave	25	1.63mm	12.7 mm
LPC126R250	Copper	Class II	Ropelay	28	1.63mm	11.94 mm

Table 2/2

Catalog Number	Длина мм	Cross Section	Unit Weight	Certifications
LPA102500	152.4m	58.31mm ²	0.05 kg	
LPA100500	152.4m	49.98mm ²	0.05 kg	cUL
LPC126R250	76.2m	58.31mm ²	0.17 kg	E202878- Combined_CoC, E202878- Combined_CoC

ADDITIONAL PRODUCT DETAILS

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

Equivalent Conductor Size	
Part Number	Conductor Size
LPC134xxx	2/0
LPC136xxx	3/0
LPC137xxx	4/0

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE