

RTBN Rail Transient Barrier Replacement Module



FEATURES

Replacement module for RTBN Rail Transient Barrier surge protection devices

SPECIFICATIONS

Catalog Number	RTBN12M	RTBN30M	RTBN50M	RTBN130M
Nominal System Voltage (Un)	12 Впост. тока 9 VAC	30 VDC 21 VAC	50 VDC 35 VAC	130 VDC 110 VAC
Color	Красный	Черный	Purple	Yellow

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE