

Special Track Work Complete Welder, Signal



FEATURES

Molds designed for conductor connections to frog and special track work applications

For use on non-load-bearing rail

Includes mold cleaner and flint ignitor

SPECIFICATIONS

Rail Type: Manganese Frog

Table 1/1

Catalog Number	Material	Bond Terminal Style	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Handle Length
SBTBTB4B	Graphite, Сталь	3/4" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4C	Graphite, Сталь	1" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4CL	Graphite, Сталь	1" Tab	3/16" Bondstrand	4.76mm	TB4	584.2mm
SBXSTB4A	Graphite, Сталь	1" Tab	3/16" Bondstrand	4.76mm	TB4	381mm
SBTBTB4E	Graphite, Сталь	1" Tab	5/16" Bondstrand	7.94mm	TB4	381mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE