

CABS Module Kit



CERTIFICATIONS



FEATURES

Modules provide flexibility to select distance between phases and supports

Installs quickly and easily

Halogen free insulators

RoHS compliant

SPECIFICATIONS

Typical Application Current Rating:	400 - 4500 A
Max Working Voltage, IEC (Ui):	1000;1500
Finish:	Electrogalvanized
Complies With:	IEC® 60439.1; IEC® 61439.1; IEC® 60695-2-11 (Glow Wire Test 960 °C)
Flammability Rating:	UL® 94V-0
Working Temperature:	-40 to 130 °C

Table 1/2

Catalog Number	Article Number	Material	Busbars per Phase	Busbar Width	Busbar Thickness	Глубина мм (D)
----------------	----------------	----------	-------------------	--------------	------------------	----------------

CABS4-5T-MOD	549370	Сталь, Glass Fibre Reinforced Polyamide	1 - 4	30 - 125 mm	5 mm	39mm
CABS2-10T-MOD	549380	Сталь, Glass Fibre Reinforced Polyamide	1 - 2	30 - 120 mm	10 mm	39mm
CABS3-10T-MOD	549390	Сталь, Glass Fibre Reinforced Polyamide	1 - 3	30 - 120 mm	10 mm	39mm

Table 2/2

Catalog Number	Article Number	Width (W)	Unit Weight
CABS4-5T-MOD	549370	75 mm	0.39 kg
CABS2-10T-MOD	549380	75 mm	0.37 kg
CABS3-10T-MOD	549390	100 mm	0.45 kg

ADDITIONAL PRODUCT DETAILS

CABS modules must be installed on CABS-APP Aluminium Profile.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE