


FTCB Flat Braid in Coil, Tinned Copper



CERTIFICATIONS



FEATURES

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

Tinned finish provides a theft-deterrent appearance

SPECIFICATIONS

Wire Diameter: 0.15mm

Material: Copper

Finish: Tinned

Table 1/2

Catalog Number	Article Number	Nominal Current	Cross Section	Number of Wires	Длина мм	Thickness
FTCB15-10	557230	75A	10mm ²	576	25m	1.5 mm
FTCB15-100	557350	360A	100mm ²	5664	25m	4 mm

CatalogNumber	Article Number	Nominal Current	Cross Section	Number of Wires	Длина мм	Thickness
FTCB15-16	557240	120A	16mm ²	896	25m	1.5 mm
FTCB15-20	557250	140A	20mm ²	1120	25m	1.5 mm
FTCB15-25	557260	150A	25mm ²	1404	25m	1.9 mm
FTCB15-3	557200	30A	3mm ²	168	25m	1 mm
FTCB15-30	557270	180A	30mm ²	1692	25m	2 mm
FTCB15-35	557280	200A	35mm ²	1980	25m	2.5 mm
FTCB15-40	557290	220A	40mm ²	2272	25m	2.5 mm
FTCB15-5	557210	45A	5mm ²	288	25m	1 mm
FTCB15-50	557300	250A	50mm ²	2848	25m	3 mm
FTCB15-60	557310	280A	60mm ²	3392	25m	3 mm
FTCB15-70	557320	290A	70mm ²	3968	25m	3.5 mm
FTCB15-75	557330	300A	75mm ²	4256	25m	4 mm
FTCB15-8	557220	65A	8mm ²	456	25m	1.5 mm
FTCB20-10	503520	75A	10mm ²	576	150m	1.5 mm
FTCB20-16	503530	120A	16mm ²	896	150m	2 mm
FTCB20-25	503540	150A	25mm ²	1404	100m	1.9 mm

Table 2/2

Catalog Number	Article Number	Width	Unit Weight
FTCB15-10	557230	10 mm	0.1 kg

Catalog Number	Article Number	Width	Unit Weight
FTCB15-100	557350	40 mm	1 kg
FTCB15-16	557240	15 mm	0.16 kg
FTCB15-20	557250	20 mm	0.2 kg
FTCB15-25	557260	18.5 mm	0.25 kg
FTCB15-3	557200	5 mm	0.03 kg
FTCB15-30	557270	23 mm	0.3 kg
FTCB15-35	557280	23 mm	0.35 kg
FTCB15-40	557290	25 mm	0.4 kg
FTCB15-5	557210	8 mm	0.05 kg
FTCB15-50	557300	28 mm	0.5 kg
FTCB15-60	557310	30 mm	0.6 kg
FTCB15-70	557320	30 mm	0.7 kg
FTCB15-75	557330	30 mm	0.75 kg
FTCB15-8	557220	8 mm	0.08 kg
FTCB20-10	503520	10 mm	0.1 kg
FTCB20-16	503530	15 mm	0.16 kg
FTCB20-25	503540	18.5 mm	0.25 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE