

MFBT-2 nVent ERIFLEX Flexibar Manual Bending Tool



CERTIFICATIONS



FEATURES

Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation

Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation

Long handle to apply force during nVent ERIFLEX Flexibar bending up to 10x120x1/12x100x1

Bending radius: 5 mm (0.20")

Allows for adjustment of the bending angle for repetitive bending

Robust blue aluminum base with three fixing points

Adjustable length setting for nVent ERIFLEX Flexibar

Quick nVent ERIFLEX Flexibar locking system with no tools required

RoHS compliant

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Conductor Width	Bending Radius	Bending Angle	Глубина мм
----------------	----------------	----------	-----------------	----------------	---------------	------------

MFBT-2	559145	Сталь, Aluminum	120 mm	5mm	120 ° Max	414mm
--------	--------	--------------------	--------	-----	-----------	-------

Table 2/2

Catalog Number	Article Number	Height	Width	Unit Weight
MFBT-2	559145	242 mm	319 mm	7 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE