

MFSHT-2 nVent ERIFLEX Flexibar Manual Shearing Tool



CERTIFICATIONS



FEATURES

Cuts nVent ERIFLEX Flexibar quickly and accurately without burrs or deformation

Cuts through the insulation without damaging it

Maximum nVent ERIFLEX Flexibar shearing 5x32x1

Adjustable abutment for identical and repetitive cuttings

Abutment and indicator allow for easy cutting of 45° chamfers

Elastomer edge near the blade helps to prevent jamming from shavings

Replacement blade available

RoHS compliant

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Conductor Thickness	Conductor Width	Глубина мм	Height
MFSHT-2	559146	Сталь, Aluminum	5 mm	32 mm Max	200mm	750 mm

Table 2/2

Catalog Number	Article Number	Width	Unit Weight
MFSHT-2	559146	160 mm	6 kg

ADDITIONAL PRODUCT DETAILS

Tool must be installed on a table.

Do not use to cut solid busbar.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE