nVent | ERIFLEX

We connect and protect

nVent ILSCO Compression Crimp - U-Dies

nVent ILSCO Compression Crimp – U Dies are part of the nVent ERICO Compression Grounding Connectors line. The U Dies are compatible with the nVent ILSCO TaskMaster tools, including the – 12-Ton Pistol Grip Crimping Tool and together they are used to crimp the compression C, and E crimp connectors in a grounding system.

The U Dies fit into the jaw of the ILSCO TaskMaster 12-ton Pistol Grip Crimping Tool and are made out of hardened stainless steel for durability and long life. U Dies are industry leading in compliance testing with ILSCO and other brand's crimps covering a broad UL compliance. Effortlessly produce secure UL listed connections with the U Dies, ILSCO tools, and ERICO C & E Compression Grounding Connectors. Dies are sold individually and in kits to cover all grounding crimp connection configurations.

FEATURES

- Durable construction produces a secure electrical connection on every crimp
- Dies are interchangeable with tools from nVent and other manufacturers
- Flexibility, compatibility, and UL compliance with other brands
- Quick and easy installation due to repeatable connections that can be made in a matter of minutes
- Use together with the ILSCO 12-ton Pistol Grip Crimping Tool to connect ERICO compression connectors
- Tested in accordance with UL467 and CSA certification

SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Длина мм	Width	Height	Unit Weight
ILD-1011	745745	Сталь	42.37mm	35.26 mm	14.22 mm	0.04 kg
ILD-998	745785	Сталь	42.72mm	35.26 mm	34.93 mm	0.1 kg
ILD-997	745735	Сталь	42.72mm	35.26 mm	34.93 mm	0.17 kg
ILD-BG	745755	Сталь	42.72mm	38.46 mm	25.4 mm	0.17 kg

CatalogNumber	Article Number	Material	Длина мм	Width	Height	Unit Weight
ILD-238	745765	Сталь	42.72mm	41.25 mm	25.4 mm	0.18 kg
ILD-D3	745715	Сталь	42.72mm	35.26 mm	34.93 mm	0.18 kg
ILD-C	745705	Сталь	42.72mm	38.46 mm	25.4 mm	0.18 kg
ILD-O	745725	Сталь	39.88mm	41.86 mm	25.4 mm	0.2 kg
ILD-162	745775	Сталь	42.72mm	41.76 mm	34.93 mm	0.3 kg

ILD-KIT-PG Includes	For use with Copper Compression Connectors
ILD-C*+	ULT-6-Z, ULT-7-Z, ELT-1
ILD-D3*+	ULT-10-Z, ULT-11-Z, ULT-12-Z, CDT-308-8, CDT-307-8
ILD-O*	GGC-1, GGA-1, GGA-2, GGA-4, ELT-2, ELT-4, CDT-304-8, CDT-303-8, ULT-8-Z, ULT-9-Z
ILD-997*+	GGA-2, GGA-3, GGA-4, GGA-5, GGA-9, GGC-2, GGC-3, GGC-4, ELT-3, ELT-5, CGP2-2250, CGP4-2250
ILD-998+	GGA-4, GGA-5, GGC-5, GGC-6, GGC-7, GGC-9, CGP2-250500, CGP4 250500, RLT-4TN, RLT-7TN, RLT-8TN, RLT-9TN, RLT-2 through RLT-13
ILD-1011+	GGA-6, GGC-8, ELT-6, ELT-7, ELT-8, RLT-4TN, RLT-7TN, RLT-8TN, RLT-9TN, RLT-2 through RLT-13
ILD-BG	ULT-3-Z, ULT-4-Z, ULT-5-Z, CST-301, CST-302, CDT-399-8, CDT-398-8
ILD-238	ULT-1-Z
ILD-162	ULT-2-Z
ILD-Precrimp	1/2, 5/8, 3/4, Ground Rod Pre Crimp Die

* May also be used with ILC-12-N, ILC-12H-N, ILCB-12-N, ILC-12, ILC-12H, ILCB-12
+ Must be used with ILD-ADP when using ILC-15, must be used with ILD-PADP when using ILC-15H

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.