

RTCB Round Braid in Coil, Tinned Copper



CERTIFICATIONS



FEATURES

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

Tinned finish provides a theft-deterrent appearance

SPECIFICATIONS

Material: Copper

Finish: Tinned

Table 1/2

Catalog Number	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Длина мм
RTCB15-10	557620	75A	10mm ²	560	0.15mm	25m
RTCB15-100	557680	360A	100mm ²	5652	0.15mm	25m
RTCB15-10HL	503700	75A	10mm ²	560	0.15mm	100m

CatalogNumber	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Длина мм
RTCB15-16	557630	120A	16mm ²	900	0.15mm	25m
RTCB15-16HL	503710	120A	16mm ²	900	0.15mm	100m
RTCB15-25	557640	150A	25mm ²	1416	0.15mm	25m
RTCB15-25HL	503720	150A	25mm ²	1416	0.15mm	100m
RTCB15-30	557650	180A	30mm ²	1680	0.15mm	25m
RTCB15-50	557660	250A	50mm ²	2820	0.15mm	25m
RTCB15-6	557600	45A	6mm ²	336	0.15mm	25m
RTCB15-75	557670	300A	75mm ²	4236	0.15mm	25m
RTCB15-8	557610	65A	8mm ²	464	0.15mm	25m

Table 2/2

Catalog Number	Article Number	Diameter	Unit Weight
RTCB15-10	557620	5 mm	0.1 kg
RTCB15-100	557680	17 mm	1 kg
RTCB15-10HL	503700	5 mm	0.1 kg
RTCB15-16	557630	6 mm	0.16 kg
RTCB15-16HL	503710	6 mm	0.16 kg
RTCB15-25	557640	8 mm	0.25 kg
RTCB15-25HL	503720	7.5 mm	0.25 kg
RTCB15-30	557650	9 mm	0.3 kg

Catalog Number	Article Number	Diameter	Unit Weight
RTCB15-50	557660	11 mm	0.5 kg
RTCB15-6	557600	4 mm	0.06 kg
RTCB15-75	557670	13.5 mm	0.75 kg
RTCB15-8	557610	4.5 mm	0.08 kg

ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE