

## , AFA

This gland plate allows for mounting FL21 gland plates, commonly used in Scandinavia.



### FEATURES

---

Description: Adapts FL gland plates to the wall mounted, steel enclosures gland opening.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

SPECIFICATIONS

**Thickness:** 1.4mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |           |           |            |                     |                  |                           |
|----------------|-----------|-----------|------------|---------------------|------------------|---------------------------|
| Catalog Number | Высота мм | Ширина мм | Глубина мм | FL Opening Quantity | Gland Plate Type | Gland Plate Opening Width |
| AFA01R5        | 2mm       | 242mm     | 128mm      | 1                   | 1, FL13          | 210mm                     |
| AFA04R5        | 2mm       | 542mm     | 128mm      | 2                   | 4, FL21          | 510mm                     |
| AFA03R5        | 2mm       | 442mm     | 128mm      | 1                   | 3, FL21          | 410mm                     |
| AFA02R5        | 2mm       | 342mm     | 128mm      | 1                   | 2, FL21          | 310mm                     |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE