

, WO60



Busbar adapter 45 A. With two adjustable mounting rails. The upper section is removable and has pre-fitted cables.

INDUSTRY STANDARDS

UL

CSA

GL

FEATURES

Description: Busbar adapter 45 A. With two adjustable mounting rails. With removable upper section and leads (10 mm²).

Rated voltage: 690 V

Rated current: 45 A

For busbars: 12, 15, 20, 25, 30 × 5, 10

Power dissipation at 80% load: 3.5 W

Poles: 3-pole

Dimensions: 54 × 200 × 75 mm

Pack quantity: 1 pc.

Approvals: CSA, UL, GL

SPECIFICATIONS

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Material	Finish	Color
32412	54mm	200mm	75mm	Plastic, Mild Steel	Plated	Черный, Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE