

Cable Entry Gland Plate Blind Cover, CEAB



Blind cover-to-cover opening for CEP and CCF cable entries.

INDUSTRY STANDARDS

UL94 V-0 Flammability; File No. E61997

NEMA Type 1, 12, 4X (indoor only)

CE

IP66

FEATURES

Description: Blind cover-to-cover openings for CEP and CCF cable entries. Mounted over the opening by using screw fixation.

Finish: Black

Flammability: UL94 V-0

Material: Polyamide 6.6 / TPE

Pack quantity: 10 pcs

Protection: IP66

Temperature resistance: -40°C to +120°C

SPECIFICATIONS

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Product Family	Material	Finish
CEAB1024	55mm	126mm	11.5mm	организация укладки кабелей	Plastic	Необработанные
CEAB816	55mm	126mm	11.5mm	организация укладки кабелей	Plastic	Необработанные

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE