

, LCR

These casters will make a fully equipped enclosure movable within a facility.



FEATURES

Description: For easy transportation of an (equipped) enclosure. Can be mounted directly to the enclosure's frame or underneath the plinths (PF/PV) with the provided mounting brackets. Raises the enclosure by 70 mm.

Maximum load: 2800 N (Moving) or 5600 N (Static) per kit.

Pack quantity: 4 pieces with mounting accessories.

SPECIFICATIONS

Material: Plastic; Plastic
Finish: Plated

Table 1/1						
Catalog Number	Высота мм	Ширина мм	Глубина мм	Caster Quantity	Brakes Included	Enclosure Material
LCR471	73mm	102mm	80mm	4	Да	Mild Steel
LCR470	73mm	102mm	80mm	4	Нет	Mild Steel
LCR472	73mm	102mm	80mm	4	Да	Mild Steel

ADDITIONAL PRODUCT DETAILS

ENC_LCR471 contains 2 casters with brakes and 2 without brakes

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE